



CLEAR VIEW® CAPS

Models: CASE-IH Quadtrac®* & ROWTRAC™* TRACTORS
(with serial #JEE0097505 and higher)

STX QUADTRAC®* 375,425,440,450,500
QUADTRAC®* 380,430,480,530;385,435,485,535; 400,450,500,550,600; 470,540,580,620
ROWTRAC™* 350,400,450,500; 370,420,470,500

INSTALLATION INSTRUCTIONS

- Remove original Case IH cap and allow oil to completely drain.
- Remove O-ring.
- Clean o-ring, housing & snap ring groove.
- Lightly oil O-ring before installing, install clear cap and secure snap ring.
- Replace lubricant in hub to manufacturer's specifications.
- Install plug. Tighten with plug wrench.

*Use only soap and water to clean caps, no solvents (solvents can cause clouding and premature failure of caps).
Solvent use will void warranty*

This kit contains both earlier (s/n 107427 and below) and later serial numbered (s/n 107428 & above) roller o-rings. Be sure you select the correct one.

PARTS LIST:

Part	Desc	Qty
K-8740-R2	Roller Cap	24
K-8743-I2	Idler Cap	16
K-1215-P	Plug	40
K-012-POR	Plug o-ring (installed)	40
K-1216-W	Plug Wrench	1
K-5426-IOR	Idler o-ring	16
K-4140-ROR	Roller o-ring(s/n 107428 & above)	24
K-2780-ROR	Roller o-ring (s/n 107427 & below)	24
	Installation Instructions	1

Kile® Clear View® Caps are covered by one or more of the following US Patent numbers: D666,227; #D689,108; #D699,772; #D700,227; #8,684,474; #8,833,872; #8,979,215; #9,120,514; #9,399,369; #9,458,965



*Quadtrac & Rowtrac are registered or trademarks CNH Corporation